



FM119

Floor standing steel enclosure, Quadro5, 2010x400x400 mm

Technical properties

Functions

Cover with overpressure release No

Configuration

Number of modules 120

Compatibility

Suitable for lightning protection No

Electric current

Rated current 630 A

Dimensions

Insertion depth 400 mm

Depth of installed product 400 mm

Internal depth 400 mm

Height of installed product 2010 mm

Width of installed product 400 mm

Width in division units 36

Thickness of sidewall material 1.2 mm

Cover, door

Material thickness cover 1.5 mm

Type of door closing non keylock

Interlockable No

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Installation, mounting

Suitable for outdoor use No

Equipment

Number of rows 13

Quantity of section in width 1

Subject to technical modifications

Number of openings for flange plates	2
Extension possible	Yes
Safety	
IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
Fire resistance	-