



FM119

**Floor standing steel enclosure, Quadro5, 2010x400x400 mm**

**Technical properties**

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 120

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Insertion depth 400 mm

Depth of installed product 400 mm

Internal depth 400 mm

Height of installed product 2010 mm

Width of installed product 400 mm

Width in division units 36

Thickness of sidewall material 1.2 mm

**Cover, door**

Material thickness cover 1.5 mm

Type of door closing non keylock

Interlockable No

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

**Installation, mounting**

Suitable for outdoor use No

**Equipment**

Number of rows 13

Quantity of section in width 1

Subject to technical modifications

Number of openings for flange plates	2
Extension possible	Yes
<b>Standards</b>	
European directive WEEE	concerned
<b>Safety</b>	
IK protection code against mechanical impacts	IK10
REACH conform	No
Fire resistance	-