



FM200

Floor standing steel enclosure, Quadro5, 510x700x260 mm

Technical properties

Configuration

Number of modules	72
-------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	260 mm
Depth of installed product	260 mm
Internal depth	260 mm
Height of installed product	510 mm
Width of installed product	700 mm
Width in division units	24
Thickness of sidewall material	2 mm

Cover, door

Cover type	Closed (plain)
Door locking	with key
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Number of conduit inlets	2
--------------------------	---

Equipment

Number of rows	3
Quantity of section in width	2
Can be accessorized	Yes
Number of openings for flange plates	2

Extension possible	Yes
Safety	
IK protection code against mechanical impacts	10
REACH conform	No
RoHS conform	Yes
Impact strength	IK10