



FM200

**Floor standing steel enclosure, Quadro5, 510x700x260 mm**

**Technical properties**

**Configuration**

Number of modules	72
-------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Insertion depth	260 mm
Depth of installed product	260 mm
Internal depth	260 mm
Height of installed product	510 mm
Width of installed product	700 mm
Width in division units	24
Thickness of sidewall material	2 mm

**Cover, door**

Cover type	Closed (plain)
Door locking	with key
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Connection**

Number of conduit inlets	2
--------------------------	---

**Equipment**

Number of rows	3
Quantity of section in width	2
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes

