



FM203

Wall mounting steel enclosure, Quadro5, 960x700x260 mm

Technical properties

Configuration

Number of modules	144
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	260 mm
Depth of installed product	260 mm
Internal depth	260 mm
Height of installed product	960 mm
Width of installed product	700 mm
Width in division units	24
Thickness of sidewall material	2 mm

Cover, door

Material thickness cover	2 mm
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	6
Quantity of section in width	2
Number of openings for flange plates	2
Extension possible	Yes

Standards

Subject to technical modifications

Safety

Protection index IP

IP55

Fire resistance

-