



FM204

**Wall mounting steel enclosure, Quadro5, 1110x700x260 mm**

**Technical properties**

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 168

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Insertion depth 260 mm

Depth of installed product 260 mm

Internal depth 260 mm

Height of installed product 1110 mm

Width of installed product 700 mm

Width in division units 24

Thickness of sidewall material 2 mm

**Cover, door**

Material thickness cover 2 mm

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Type of surface treatment powder-coated

**Installation, mounting**

Suitable for outdoor use No

**Equipment**

Number of rows 7

Quantity of section in width 2

Number of openings for flange plates 2

Subject to technical modifications

Extension possible	Yes
<b>Safety</b>	
IK protection code against mechanical impacts	IK10
REACH conform	No
RoHS conform	Yes
Fire resistance	-