



FM205

**Wall mounting steel enclosure, Quadro5, 1260x700x260mm**

**Technical properties**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Configuration**

Number of modules	192
-------------------	-----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Insertion depth	260 mm
Depth of installed product	260 mm
Internal depth	260 mm
Height of installed product	1260 mm
Width of installed product	700 mm
Width in division units	24
Thickness of sidewall material	2 mm

**Cover, door**

Cover type	Closed (plain)
Door locking	with key
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel
Type of surface treatment	powder-coated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Connection**

Number of conduit inlets	2
--------------------------	---

**Equipment**

Number of rows	8
Quantity of section in width	2

Subject to technical modifications

Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes

---

**Standards**

European directive WEEE	concerned
-------------------------	-----------

---

**Safety**

IK protection code against mechanical impacts	10
REACH conform	No
RoHS conform	Yes
Impact strength	IK10