



FM205

Wall mounting steel enclosure, Quadro5, 1260x700x260mm

Technical properties

Functions

| | |
|---------------------------------|----|
| Cover with overpressure release | No |
|---------------------------------|----|

Configuration

| | |
|-------------------|-----|
| Number of modules | 192 |
|-------------------|-----|

Electric current

| | |
|---------------|-------|
| Rated current | 630 A |
|---------------|-------|

Dimensions

| | |
|--------------------------------|---------|
| Insertion depth | 260 mm |
| Depth of installed product | 260 mm |
| Internal depth | 260 mm |
| Height of installed product | 1260 mm |
| Width of installed product | 700 mm |
| Width in division units | 24 |
| Thickness of sidewall material | 2 mm |

Cover, door

| | |
|---------------------------|----------------|
| Cover type | Closed (plain) |
| Door locking | with key |
| Door leave | single |
| Cover type | Door |
| Transparent cover or door | No |

Materials

| | |
|------------|-----------------------|
| Colour | pure white |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | Steel |

Installation, mounting

| | |
|--------------------------|----|
| Suitable for outdoor use | No |
|--------------------------|----|

Connection

| | |
|--------------------------|---|
| Number of conduit inlets | 2 |
|--------------------------|---|

Equipment

| | |
|------------------------------|-----|
| Number of rows | 8 |
| Quantity of section in width | 2 |
| Can be accessorized | Yes |

Subject to technical modifications

| | |
|--------------------------------------|-----------|
| Number of openings for flange plates | 2 |
| Extension possible | Yes |
| Standards | |
| European directive WEEE | concerned |
| Safety | |
| Protection index IP | IP55 |
