



FM206

Wall mounting steel enclosure, Quadro5, 1410x700x260 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	216
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	260 mm
Depth of installed product	260 mm
Internal depth	260 mm
Height of installed product	1410 mm
Width of installed product	700 mm
Width in division units	24
Thickness of sidewall material	2 mm

Cover, door

Material thickness cover	2 mm
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	9
Quantity of section in width	2

Subject to technical modifications

Number of openings for flange plates	2
Extension possible	Yes
Standards	
European directive WEEE	concerned
Safety	
IK protection code against mechanical impacts	IK10
Protection index IP	IP55
REACH conform	No
RoHS conform	Yes
Fire resistance	-