



FM207

Floor standing steel enclosure, Quadro5, 1710x700x260 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	240
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	260 mm
-----------------	--------

Depth of installed product	260 mm
----------------------------	--------

Internal depth	260 mm
----------------	--------

Height of installed product	1710 mm
-----------------------------	---------

Width of installed product	700 mm
----------------------------	--------

Width in division units	24
-------------------------	----

Thickness of sidewall material	2 mm
--------------------------------	------

Cover, door

Material thickness cover	2 mm
--------------------------	------

Cover type	Closed (plain)
------------	----------------

Door leave	single
------------	--------

Cover type	Door
------------	------

Transparent cover or door	No
---------------------------	----

Materials

Colour	pure white
--------	------------

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	Steel
----------	-------

Type of surface treatment	powder-coated
---------------------------	---------------

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	10
----------------	----

Quantity of section in width	2
------------------------------	---

Subject to technical modifications

Number of openings for flange plates	2
Extension possible	Yes
Standards	
European directive WEEE	concerned
Safety	
IK protection code against mechanical impacts	IK10
REACH conform	No
Fire resistance	-