



FM207

Floor standing steel enclosure, Quadro5, 1710x700x260 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	240
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	260 mm
Depth of installed product	260 mm
Internal depth	260 mm
Height of installed product	1710 mm
Width of installed product	700 mm
Width in division units	24
Thickness of sidewall material	2 mm

Cover, door

Material thickness cover	2 mm
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	10
Quantity of section in width	2
Number of openings for flange plates	2

Extension possible

Yes

Standards

European directive WEEE

concerned

Safety

Protection index IP

IP55

Fire resistance

-