



FM208

**Floor standing steel enclosure, Quadro5, 1860x700x260 mm**

**Technical properties**

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 264

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Insertion depth 260 mm

Depth of installed product 260 mm

Internal depth 260 mm

Height of installed product 1860 mm

Width of installed product 700 mm

Width in division units 24

Thickness of sidewall material 2 mm

**Cover, door**

Material thickness cover 2 mm

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Type of surface treatment powder-coated

**Installation, mounting**

Suitable for outdoor use No

**Equipment**

Number of rows 12

Quantity of section in width 2

Number of openings for flange plates 2

Subject to technical modifications

---

Extension possible

Yes

**Safety**

---

IK protection code against mechanical impacts

IK10

---

REACH conform

No

---

Fire resistance

-