



FM219

Floor standing steel enclosure, Quadro5, 2010x700x400 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	288
-------------------	-----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Insertion depth	400 mm
Depth of installed product	400 mm
Internal depth	400 mm
Height of installed product	2010 mm
Width of installed product	700 mm
Width in division units	36
Thickness of sidewall material	1.2 mm

Cover, door

Material thickness cover	1.5 mm
Type of door closing	non keylock
Interlockable	No
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	13
Quantity of section in width	2

Subject to technical modifications

Number of openings for flange plates	2
Extension possible	Yes
Standards	
European directive WEEE	concerned
Safety	
IK protection code against mechanical impacts	IK10
REACH conform	No
Fire resistance	-