



FM308

Floor standing steel enclosure, Quadro5, 1860x900x260 mm

Technical properties

Functions

Cover with overpressure release No

Configuration

Number of modules 396

Compatibility

Suitable for lightning protection No

Electric current

Rated current 630 A

Dimensions

Insertion depth 260 mm

Depth of installed product 260 mm

Internal depth 260 mm

Height of installed product 1860 mm

Width of installed product 900 mm

Width in division units 36

Thickness of sidewall material 2 mm

Cover, door

Material thickness cover 2 mm

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Type of surface treatment powder-coated

Installation, mounting

Suitable for outdoor use No

Equipment

Number of rows 12

Quantity of section in width 3

Number of openings for flange plates 2

Subject to technical modifications

Extension possible

Yes

Safety

IK protection code against mechanical impacts

IK10

REACH conform

No

Fire resistance

-