



FM308

**Floor standing steel enclosure, Quadro5, 1860x900x260 mm**

**Technical properties**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Configuration**

Number of modules	396
-------------------	-----

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Insertion depth	260 mm
Depth of installed product	260 mm
Internal depth	260 mm
Height of installed product	1860 mm
Width of installed product	900 mm
Width in division units	36
Thickness of sidewall material	2 mm

**Cover, door**

Material thickness cover	2 mm
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Equipment**

Number of rows	12
Quantity of section in width	3
Number of openings for flange plates	2

---

Extension possible

Yes

---

**Standards**

European directive WEEE

concerned

---

**Safety**

Protection index IP

IP55

Fire resistance

-