



FM319

**Floor standing steel enclosure, Quadro5, 2010x900x400 mm**

**Technical properties**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Configuration**

Number of modules	432
-------------------	-----

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Insertion depth	400 mm
Depth of installed product	400 mm
Internal depth	400 mm
Height of installed product	2010 mm
Width of installed product	900 mm
Width in division units	36
Thickness of sidewall material	1.2 mm

**Cover, door**

Material thickness cover	1.5 mm
Type of door closing	non keylock
Interlockable	No
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	metal
Type of surface treatment	Galvanised

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Equipment**

Subject to technical modifications

Number of rows	13
Quantity of section in width	3
Number of openings for flange plates	2
Extension possible	Yes

---

**Standards**

European directive WEEE	concerned
-------------------------	-----------

---

**Safety**

Protection index IP	IP55
Protection class	isol.class I
Fire resistance	-