



FN004E

Corner Structure, quadro evo 400x400x1900

Technical properties

Architecture

Intended door position	right
------------------------	-------

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	0
-------------------	---

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	1600 A
---------------	--------

Dimensions

Insertion depth	400 mm
Depth of installed product	400 mm
Internal depth	300 mm
Height of installed product	1900 mm
Width of installed product	400 mm
Thickness of sidewall material	1.5 mm

Cover, door

Material thickness cover	2 mm
Identification od protection index	55
Interlockable	No
Cover type	Closed (plain)
Cover type	Cover
Transparent cover or door	No

Materials

RAL colour	RAL 9010 - Pure white
Material	Steel
Type of surface treatment	Painted

Installation, mounting

Suitable for outdoor use	No
Suitable for ground mounting	Yes

Scope of delivery

With cover	Yes
Equipment	
Number of rows	0
Quantity of rails	0
On/Off switch	No
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Safety	
Protection index IP	IP55
Protection class	isol.class I
Fire resistance	-