



FN004E

Corner Structure, quadro evo 400x400x1900

Technical properties

Architecture

Intended door position right

Functions

Cover with overpressure release No

Configuration

Number of modules 0

Compatibility

Suitable for lightning protection No

Electric current

Rated current 1600 A

Dimensions

Insertion depth 400 mm

Depth of installed product 400 mm

Internal depth 300 mm

Height of installed product 1900 mm

Width of installed product 400 mm

Thickness of sidewall material 1.5 mm

Cover, door

Material thickness cover 2 mm

Identification of protection index 55

Interlockable No

Cover type Closed (plain)

Cover type Cover

Transparent cover or door No

Materials

RAL colour RAL 9010 - Pure white

Surface appearance glossy

Installation, mounting

Suitable for outdoor use No

Suitable for ground mounting Yes

Scope of delivery

With cover Yes

Equipment

Number of rows	0
Quantity of rails	0
On/Off switch	No
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes

Standards

Approvals	EN 61439-1/-2
-----------	---------------

Safety

IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	Yes
Fire resistance	-