



FN005E

**Corner Structure, quadro evo 400x400x2100**

**Technical properties**

**Architecture**

Intended door position right

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 0

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 1600 A

**Dimensions**

Insertion depth 400 mm

Depth of installed product 400 mm

Internal depth 300 mm

Height of installed product 2100 mm

Width of installed product 400 mm

Thickness of sidewall material 1.5 mm

**Cover, door**

Material thickness cover 2 mm

Identification of protection index 55

Interlockable No

Cover type Closed (plain)

Cover type Cover

Transparent cover or door No

**Materials**

RAL colour RAL 9010 - Pure white

Surface appearance glossy

**Installation, mounting**

Suitable for outdoor use No

Suitable for ground mounting Yes

**Scope of delivery**

With cover Yes

**Equipment**

Number of rows	0
Quantity of rails	0
On/Off switch	No
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes

**Standards**

Approvals	EN 61439-1/-2
-----------	---------------

**Safety**

IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	Yes
Fire resistance	-