



FN013EW

Top & bottom, quadro evo, 700x800 mm

Technical properties

Dimensions

Insertion depth	800 mm
Depth of installed product	800 mm
Height of installed product	50 mm
Width of installed product	700 mm
Built-in width	700 mm

Materials

RAL colour	RAL 9010 - Pure white
Surface appearance	glossy

Installation, mounting

Suitable for outdoor use	No
With cable entry	No

Standards

Approvals	EN 61439-1/-2
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	10
REACH conform	No
RoHS conform	Yes
Halogen free	Yes