



FN017EW

Top & bottom, quadro evo, 900x800 mm

Technical properties

Dimensions

Insertion depth	800 mm
Depth of installed product	800 mm
Height of installed product	50 mm
Width of installed product	900 mm
Built-in width	900 mm

Materials

Colour	white (shades)
RAL colour	RAL 9010 - Pure white
Material	other
Surface appearance	glossy
Type of surface treatment	Painted

Installation, mounting

Suitable for outdoor use	No
With cable entry	No

Standards

Approvals	EN 61439-1/-2
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	10
---	----