



FN286EW

vertical dividing uprights, quadro evo, 1900mm

Technical properties

Configuration

Number of modules	0
-------------------	---

Dimensions

Depth of installed product	50 mm
Height of installed product	1800 mm
Length	1800 mm
Width of installed product	100 mm
Material thickness	1.5 mm

Materials

Type of surface treatment	Other
---------------------------	-------

Standards

Approvals	EN 61439-1/-2
European directive WEEE	not concerned

Safety

REACH conform	No
RoHS conform	Yes