



FN6020FDW

Modular fix panel, quadro evo 600x200

Technical properties

Architecture

Intended door position	right
------------------------	-------

Dimensions

Depth of installed product	40 mm
Height of installed product	200 mm
Width of installed product	700 mm
Built-in height	200 mm

Cover, door

Number of keylock of the door	0
Door type for switch gear cabinet	Partial door
Door leave	single
Transparent cover or door	No

Materials

RAL colour	RAL 9010 - Pure white
Surface appearance	glossy

Equipment

Number of rows	0
----------------	---

Standards

Approvals	EN 61439-1/-2
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	Yes