



FN6020FDW

Modular fix panel, quadro evo 600x200

Technical properties

Architecture

Intended door position right

Dimensions

Depth of installed product 40 mm

Height of installed product 200 mm

Width of installed product 700 mm

Built-in height 200 mm

Cover, door

Number of keylock of the door 0

Door type for switch gear cabinet Partial door

Door leave single

Transparent cover or door No

Materials

RAL colour RAL 9010 - Pure white

Surface appearance glossy

Equipment

Number of rows 0

Standards

Approvals EN 61439-1/-2

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 10

Protection class isol.class I

REACH conform No

RoHS conform Yes

Halogen free Yes