



FN6020MDW

**Modular DIN door, quadro evo 600x200**

**Technical properties**

**Architecture**

Intended door position right

**Dimensions**

Depth of installed product 40 mm

Height of installed product 200 mm

Width of installed product 600 mm

Built-in height 200 mm

**Cover, door**

Number of keylock of the door 1

Door type for switch gear cabinet Partial door

Door leave single

Transparent cover or door No

**Materials**

RAL colour RAL 9010 - Pure white

Surface appearance glossy

**Settings**

Angle range 0 / 120 °

**Equipment**

Number of rows 0

**Standards**

Approvals EN 61439-1/-2

**Safety**

IK protection code against mechanical impacts 10

Protection class isol.class I

REACH conform No

RoHS conform Yes