



FN6020MDW

Modular DIN door, quadro evo 600x200

Technical properties

Architecture

Intended door position	right
------------------------	-------

Dimensions

Depth of installed product	40 mm
Height of installed product	200 mm
Width of installed product	600 mm
Built-in height	200 mm

Cover, door

Number of keylock of the door	1
Door type for switch gear cabinet	Partial door
Door leave	single
Transparent cover or door	No

Materials

RAL colour	RAL 9010 - Pure white
Material	Steel
Surface appearance	glossy

Settings

Angle range	0 / 120 °
-------------	-----------

Equipment

Number of rows	0
----------------	---

Safety

IK protection code against mechanical impacts	10
REACH conform	No
RoHS conform	Yes