



FN6020PDW

Modular door, quadro evo 600x200

Technical properties

Architecture

Intended door position	right
------------------------	-------

Dimensions

Depth of installed product	43 mm
Height of installed product	200 mm
Width of installed product	700 mm
Built-in height	200 mm

Cover, door

Type of door closing	lock with male triangular wrench
Number of keylock of the door	1
Door type for switch gear cabinet	Partial door
Door leave	single
Transparent cover or door	No

Materials

RAL colour	RAL 9010 - Pure white
Material	Steel
Type of surface treatment	Painted

Settings

Angle range	0 / 120 °
-------------	-----------

Equipment

Number of rows	0
Number of keys	1

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection class	isol.class I
------------------	--------------