



FN6040PDW

Modular door, quadro evo 600x400

Technical properties

Architecture

Intended door position right

Dimensions

Depth of installed product 43 mm

Height of installed product 400 mm

Width of installed product 700 mm

Built-in height 400 mm

Cover, door

Type of door closing lock with male triangular wrench

Number of keylock of the door 2

Door type for switch gear cabinet Partial door

Door leave single

Transparent cover or door No

Materials

RAL colour RAL 9010 - Pure white

Material Steel

Type of surface treatment Painted

Settings

Angle range 0 / 120 °

Equipment

Number of rows 0

Quantity of section in width 2

Standards

European directive WEEE not concerned

Safety

Protection class isol.class I