



FN6040PGW

Modular glass door, quadro evo 600x400

Technical properties

Architecture

Intended door position right

Dimensions

Depth of installed product 43 mm

Height of installed product 400 mm

Width of installed product 700 mm

Built-in height 400 mm

Cover, door

Number of keylock of the door 2

Door type for switch gear cabinet Partial door

Door leave single

Transparent cover or door Yes

Materials

RAL colour RAL 9010 - Pure white

Surface appearance glossy

Settings

Angle range 0 / 120 °

Equipment

Number of rows 0

Quantity of section in width 2

Standards

Approvals EN 61439-1/-2

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 10

Protection class isol.class I

REACH conform No

RoHS conform Yes

Halogen free No