



FN6060PGW

Modular glass door, quadro evo 600x600

Technical properties

Architecture

Intended door position	right
------------------------	-------

Dimensions

Depth of installed product	43 mm
Height of installed product	600 mm
Width of installed product	700 mm
Built-in height	600 mm

Cover, door

Number of keylock of the door	2
Door type for switch gear cabinet	Partial door
Door leave	single
Transparent cover or door	Yes

Materials

RAL colour	RAL 9010 - Pure white
Surface appearance	glossy

Settings

Angle range	0 / 120 °
-------------	-----------

Equipment

Number of rows	0
Quantity of section in width	2
Number of keys	2

Standards

Approvals	EN 61439-1/-2
European directive WEEE	not concerned

Safety

IK protection code against mechanical impacts	10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	No