



FN6060PGW

**Modular glass door, quadro evo 600x600**

**Technical properties**

**Architecture**

Intended door position	right
------------------------	-------

**Dimensions**

Depth of installed product	43 mm
Height of installed product	600 mm
Width of installed product	700 mm
Built-in height	600 mm

**Cover, door**

Number of keylock of the door	2
Door type for switch gear cabinet	Partial door
Door leave	single
Transparent cover or door	Yes

**Materials**

RAL colour	RAL 9010 - Pure white
Surface appearance	glossy

**Settings**

Angle range	0 / 120 °
-------------	-----------

**Equipment**

Number of rows	0
Quantity of section in width	2
Number of keys	2

**Standards**

Approvals	EN 61439-1/-2
European directive WEEE	not concerned

**Safety**

IK protection code against mechanical impacts	10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	No