



FN8020FDW

Modular fix panel, quadro evo 800x200

Technical properties

Architecture

Intended door position right

Dimensions

Depth of installed product 40 mm

Height of installed product 200 mm

Width of installed product 900 mm

Built-in height 200 mm

Cover, door

Number of keylock of the door 0

Door type for switch gear cabinet Partial door

Door leave single

Transparent cover or door No

Materials

RAL colour RAL 9010 - Pure white

Material Steel

Type of surface treatment Painted

Equipment

Number of rows 0

Standards

European directive WEEE not concerned

Safety

Protection class isol.class I