



FN8020MDW

### Modular DIN door, quadro evo 800x200

#### Technical properties

##### Architecture

Intended door position	right
------------------------	-------

##### Dimensions

Depth of installed product	40 mm
Height of installed product	200 mm
Width of installed product	800 mm
Built-in height	200 mm

##### Cover, door

Type of door closing	lock with male triangular wrench
Number of keylock of the door	1
Door type for switch gear cabinet	Partial door
Door leave	single
Transparent cover or door	No

##### Materials

RAL colour	RAL 9010 - Pure white
Material	Steel
Type of surface treatment	Painted

##### Equipment

Number of rows	0
----------------	---

##### Safety

Protection class	isol.class I
------------------	--------------