



FN8020PDW

Modular door, quadro evo 800x200

Technical properties

Architecture

Intended door position right

Dimensions

Depth of installed product 43 mm

Height of installed product 200 mm

Width of installed product 900 mm

Built-in height 200 mm

Cover, door

Type of door closing lock with male triangular wrench

Number of keylock of the door 1

Door type for switch gear cabinet Partial door

Door leave single

Transparent cover or door No

Materials

Colour white (shades)

RAL colour RAL 9010 - Pure white

Material Steel

Surface appearance glossy

Type of surface treatment Painted

Settings

Angle range 0 / 120 °

Equipment

Number of rows 0

Number of keys 1

Standards

Approvals EN 61439-1/-2

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts 10

Protection index IP IP43

Protection class isol.class I