



FV22A

**Surface enclosure, VegaD IP55, 500x550x275mm, with 2 rows to complete**

**Technical properties**

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Configuration**

Number of modules	0
-------------------	---

**Electric current**

Rated current	160 A
---------------	-------

**Dimensions**

Depth of installed product	275 mm
Internal depth	218 mm
Height of installed product	500 mm
Width of installed product	550 mm
Width in division units	24
Thickness of sidewall material	2 mm

**Cover, door**

Cover type	Closed (plain)
Door locking	with special tool
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	white
RAL colour	RAL 9010 - Pure white
Material	Plastic/metal
Type of surface treatment	powder-coated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Connection**

Number of conduit inlets	4
--------------------------	---

**Scope of delivery**

With cover	Yes
------------	-----

**Equipment**

Number of rows	2
----------------	---

Quantity of section in width	1
Number of keys	1
Quantity of rails	0
Can be accessorized	Yes
Number of openings for flange plates	4
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	No

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

IK protection code against mechanical impacts	IK10
Protection index IP	IP55
Protection class	isol.class II
REACH conform	No