



FWB31D



FWB encl.,univers, 3rows 36mod. IP44 cl.II empty w.plain door,500x300x161mm

Technical properties

Configuration

Number of modules 36

Compatibility

Suitable for lightning protection No

Electric current

Rated current 125 A

Dimensions

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 500 mm

Installation height 500 mm

Width of installed product 300 mm

Width in division units 12

Thickness of sidewall material 1 mm

Housing installation depth 161 mm

Cover, door

Material thickness cover 2.5 mm

Type of door closing hinged pattern handle

Interlockable No

Number of keylock of the door 1

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour white

Colour white

RAL colour RAL 9010 - Pure white

Type of surface treatment powder-coated

Installation, mounting

Suitable for outdoor use No

Settings

Enclosure type Field distributor surface mounted

Equipment

Number of rows	0
Quantity of section in width	1
Number of keys	1
Quantity of rails	3
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	No

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK09
Protection index IP	IP44
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Fire resistance	-