



FWB31GS

**FWB encl.,univers,surface mount.,IP44,classII,w. transp.door,500x300x161mm,QC**

## Technical properties

### Architecture

Fixing mode	surface-mounting
-------------	------------------

### Functions

With a pipe-in lead	Yes
---------------------	-----

### Configuration

Number of modules	36
-------------------	----

### Compatibility

Suitable for Multimedia	No
-------------------------	----

### Electric current

Rated current	125 A
---------------	-------

### Dimensions

Depth of installed product	165 mm
----------------------------	--------

Internal depth	156 mm
----------------	--------

Height of installed product	500 mm
-----------------------------	--------

Installation height	500 mm
---------------------	--------

Width of installed product	300 mm
----------------------------	--------

Width in division units	12
-------------------------	----

Thickness of sidewall material	1 mm
--------------------------------	------

### Cover, door

Number of keylock of the door	1
-------------------------------	---

Cover type	With Notch
------------	------------

Door leave	single
------------	--------

Cover type	Door
------------	------

Transparent cover or door	Yes
---------------------------	-----

### Materials

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	Steel
----------	-------

Type of surface treatment	powder-coated
---------------------------	---------------

### Installation, mounting

Suitable for outdoor use	No
--------------------------	----

### Connection

**Equipment**

Number of rows	3
Quantity of section in width	1
Number of keys	1
Quantity of rails	3
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	No

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

IK protection code against mechanical impacts	IK07
Protection index IP	IP44
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No