



FWB32GS

FWB encl.,univers,surface mount.,IP44,classII,w. transp.door,500x550x161mm,QC

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Module with terminals

Number of modules 72

Compatibility

Suitable for Multimedia No

Electric current

Rated current 125 A

Dimensions

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 500 mm

Installation height 500 mm

Width of installed product 550 mm

Width in division units 24

Thickness of sidewall material 1 mm

Cover, door

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

Installation, mounting

Suitable for outdoor use No

Settings

Enclosure type

Field distributor surface mounted

Equipment

Number of rows	6
Quantity of section in width	2
Number of keys	1
Can be accessorized	Yes
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	No

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP44
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No