



FWB32S

**FWB encl.,univers, 3rows 72 modules cl.II IP44 w.plain door, 500x550x161mm,QC**

**Technical properties**

**Functions**

With a pipe-in lead	Yes
Protection main switch	No

**Configuration**

Module	with terminals
Number of modules	72

**Compatibility**

Suitable for Multimedia	No
-------------------------	----

**Electric current**

Rated current	125 A
---------------	-------

**Dimensions**

Insertion depth	161 mm
Depth of installed product	165 mm
Internal depth	156 mm
Height of installed product	500 mm
Installation height	500 mm
Width of installed product	550 mm
Width in division units	24
Thickness of sidewall material	1 mm

**Cover, door**

Type of door closing	hinged pattern handle
Number of keylock of the door	1
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Copper weight of the product	0.069 kg
Colour	white
RAL colour	RAL 9010 - Pure white
Material	sheet steel

**Installation, mounting**

Suitable for outdoor use No

### Connection

Number of conduit inlets 8

### Settings

Enclosure type Field distributor surface mounted

### Equipment

Number of rows 3

Quantity of section in width 2

Number of keys 1

Can be accessorized Yes

Number of openings for flange plates 4

Extension possible Yes

Earthing terminal block Yes

Neutral terminal block Yes

Signal passing door No

### Standards

GWT Glow wire test 750 °C

Protection class according to IEC-61140 II

### Safety

IK protection code against mechanical impacts 09

Protection index IP IP44

Protection class isol.class II

REACH conform No

RoHS conform Yes

Halogen free No

Impact strength IK09