



FWB33GS

FWB encl.,univers,surface mount.,IP44,classII,w. transp.door,500x800x161mm,QC

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Module with terminals

Number of modules 108

Compatibility

Suitable for Multimedia No

Electric current

Rated current 125 A

Dimensions

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 500 mm

Installation height 500 mm

Width of installed product 800 mm

Width in division units 36

Thickness of sidewall material 1 mm

Cover, door

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door leave double asymmetric

Cover type Door

Transparent cover or door Yes

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

Type of surface treatment powder-coated

Installation, mounting

Suitable for outdoor use No

Subject to technical modifications

Connection

Number of conduit inlets	12
--------------------------	----

Settings

Enclosure type	Field distributor surface mounted
----------------	-----------------------------------

Equipment

Number of rows	9
----------------	---

Quantity of section in width	3
------------------------------	---

Number of keys	1
----------------	---

Quantity of rails	9
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	6
--------------------------------------	---

Extension possible	Yes
--------------------	-----

Earthing terminal block	Yes
-------------------------	-----

Neutral terminal block	Yes
------------------------	-----

Signal passing door	No
---------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	IK07
-----------------------------------------------	------

Protection index IP	IP44
---------------------	------

Protection class	isol.class II
------------------	---------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----