



FWB34GS

**FWB encl. univers,surface mount.,IP44,classII,w. transp.door,500x1050x161mm,QC**

**Technical properties**

**Functions**

With a pipe-in lead Yes

**Configuration**

Module with terminals

Number of modules 144

**Compatibility**

Suitable for Multimedia No

**Electric current**

Rated current 125 A

**Dimensions**

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 500 mm

Installation height 500 mm

Width of installed product 1050 mm

Width in division units 48

Thickness of sidewall material 1 mm

**Cover, door**

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type Closed (plain)

Door leave double asymmetric

Cover type Door

Transparent cover or door Yes

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Type of surface treatment powder-coated

**Installation, mounting**

Suitable for outdoor use No

**Connection**

Number of conduit inlets 16

**Settings**

---

Enclosure type	Field distributor surface mounted
----------------	-----------------------------------

**Equipment**

---

Number of rows	12
Quantity of section in width	4
Number of keys	1
Quantity of rails	12
Can be accessorized	Yes
Number of openings for flange plates	8
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	No

**Safety**

---

IK protection code against mechanical impacts	IK07
Protection index IP	IP44
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No