



FWB34S

FWB encl. univers,3-rows 144 modules cl.II IP44 w.plain door, 500x1050x161mm,QC

Technical properties

Architecture

| | |
|-------------|------------------|
| Fixing mode | surface-mounting |
|-------------|------------------|

Functions

| | |
|---------------------|-----|
| With a pipe-in lead | Yes |
|---------------------|-----|

Configuration

| | |
|-------------------|-----|
| Number of modules | 144 |
|-------------------|-----|

Compatibility

| | |
|-------------------------|----|
| Suitable for Multimedia | No |
|-------------------------|----|

Electric current

| | |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

Dimensions

| | |
|--------------------------------|---------|
| Depth of installed product | 165 mm |
| Internal depth | 156 mm |
| Height of installed product | 500 mm |
| Installation height | 500 mm |
| Width of installed product | 1050 mm |
| Width in division units | 48 |
| Thickness of sidewall material | 1 mm |

Cover, door

| | |
|-------------------------------|------------|
| Number of keylock of the door | 1 |
| Cover type | With Notch |
| Door locking | without |
| Door leave | single |
| Cover type | Door |
| Transparent cover or door | No |

Materials

| | |
|------------------------------|-----------------------|
| Copper weight of the product | 0.135 kg |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | sheet steel |

Installation, mounting

| | |
|--------------------------|----|
| Suitable for outdoor use | No |
|--------------------------|----|

Connection

| | |
|--------------------------|----|
| Number of conduit inlets | 16 |
|--------------------------|----|

Equipment

| | |
|--------------------------------------|-----|
| Number of rows | 3 |
| Quantity of section in width | 4 |
| Number of keys | 1 |
| Quantity of rails | 12 |
| Can be accessorized | Yes |
| Number of openings for flange plates | 8 |
| Extension possible | Yes |
| Earthing terminal block | Yes |
| Neutral terminal block | Yes |
| Signal passing door | No |

Standards

| | |
|---|-----------|
| European directive WEEE | concerned |
| Protection class according to IEC-61140 | II |

Safety

| | |
|---------------------|---------------|
| Protection index IP | IP44 |
| Protection class | isol.class II |
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |