



FWB34S

FWB encl. univers,3-rows 144 modules cl.II IP44 w.plain door, 500x1050x161mm,QC

Technical properties

Functions

With a pipe-in lead Yes

Configuration

Module with terminals

Number of modules 144

Compatibility

Suitable for Multimedia No

Electric current

Rated current 125 A

Dimensions

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 500 mm

Installation height 500 mm

Width of installed product 1050 mm

Width in division units 48

Thickness of sidewall material 1 mm

Cover, door

Type of door closing Hinged pattern handle and bar locking

Number of keylock of the door 1

Cover type With Notch

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Copper weight of the product 0.135 kg

Colour white

RAL colour RAL 9010 - Pure white

Material sheet steel

Installation, mounting

Suitable for outdoor use No

Connection

Subject to technical modifications

Settings

Enclosure type	Field distributor surface mounted
----------------	-----------------------------------

Equipment

Number of rows	3
Quantity of section in width	4
Number of keys	1
Quantity of rails	12
Can be accessorized	Yes
Number of openings for flange plates	8
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	No

Standards

Protection class according to IEC-61140	II
---	----

Safety

IK protection code against mechanical impacts	09
Protection index IP	IP44
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK09