



FWB42

FWB encl.,univers,4rows 48 mod cl.II IP44,plain door,650x300x161mm,brass term.

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes
Protection main switch No

Configuration

Number of modules 96

Compatibility

Suitable for Multimedia No

Electric current

Rated current 125 A

Dimensions

Insertion depth 161 mm
Depth of installed product 165 mm
Internal depth 156 mm
Height of installed product 650 mm
Installation height 650 mm
Width of installed product 550 mm
Width in division units 24
Thickness of sidewall material 2 mm

Cover, door

Type of door closing hinged pattern handle
Number of keylock of the door 1
Cover type With Notch
Door locking without
Door leave single
Cover type Door
Transparent cover or door No

Materials

Colour white
Colour white
RAL colour RAL 9010 - Pure white

Installation, mounting

Subject to technical modifications

Suitable for outdoor use

No

Connection

Number of conduit inlets 8

Settings

Enclosure type Field distributor surface mounted

Equipment

Number of rows 8

Quantity of section in width 2

Number of keys 1

Quantity of rails 8

Can be accessorized Yes

Number of openings for flange plates 4

Extension possible Yes

Earthing terminal block No

Neutral terminal block Yes

Signal passing door No

Standards

GWT Glow wire test 750 °C

European directive WEEE concerned

Protection class according to IEC-61140 II

Safety

Protection index IP IP44

Protection class isol.class II