



FWB42

**FWB encl.,univers,4rows 48 mod cl.II IP44,plain door,650x300x161mm,brass term.**

## Technical properties

### Architecture

Fixing mode	surface-mounting
-------------	------------------

### Functions

With a pipe-in lead	Yes
Protection main switch	No

### Configuration

Number of modules	96
-------------------	----

### Compatibility

Suitable for Multimedia	No
-------------------------	----

### Electric current

Rated current	125 A
---------------	-------

### Dimensions

Insertion depth	161 mm
Depth of installed product	165 mm
Internal depth	156 mm
Height of installed product	650 mm
Installation height	650 mm
Width of installed product	550 mm
Width in division units	24
Thickness of sidewall material	2 mm

### Cover, door

Number of keylock of the door	1
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

### Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	sheet steel

### Installation, mounting

Subject to technical modifications

Suitable for outdoor use	No
<b>Connection</b>	
Number of conduit inlets	8
<b>Equipment</b>	
Number of rows	8
Quantity of section in width	2
Number of keys	1
Quantity of rails	8
Can be accessorized	Yes
Number of openings for flange plates	4
Extension possible	Yes
Earthing terminal block	No
Neutral terminal block	Yes
Signal passing door	No
<b>Standards</b>	
GWT Glow wire test	750 °C
European directive WEEE	concerned
Protection class according to IEC-61140	II
<b>Safety</b>	
Protection index IP	IP44
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No