



FWB42GS

**FWB encl. univers,surface mount.,IP44,classII,w. transp.door,650x550x161mm,QC**

**Technical properties**

**Functions**

With a pipe-in lead Yes

**Configuration**

Module with terminals

Number of modules 96

**Compatibility**

Suitable for Multimedia No

**Electric current**

Rated current 125 A

**Dimensions**

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 650 mm

Installation height 650 mm

Width of installed product 550 mm

Width in division units 24

Thickness of sidewall material 1 mm

**Cover, door**

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

**Installation, mounting**

Suitable for outdoor use No

**Settings**

Enclosure type Field distributor surface mounted

**Equipment**

Number of rows	8
Quantity of section in width	2
Number of keys	1
Quantity of rails	8
Can be accessorized	Yes
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	No

#### **Safety**

Protection index IP	IP44
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No