



FWB42GS

**FWB encl. univers,surface mount.,IP44,classII,w. transp.door,650x550x161mm,QC**

### Technical properties

#### Architecture

Fixing mode surface-mounting

#### Functions

With a pipe-in lead Yes

#### Configuration

Module with terminals

Number of modules 96

#### Compatibility

Suitable for Multimedia No

#### Electric current

Rated current 125 A

#### Dimensions

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 650 mm

Installation height 650 mm

Width of installed product 550 mm

Width in division units 24

Thickness of sidewall material 1 mm

#### Cover, door

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door Yes

#### Materials

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

#### Installation, mounting

Suitable for outdoor use No

**Settings**

---

|                |                                   |
|----------------|-----------------------------------|
| Enclosure type | Field distributor surface mounted |
|----------------|-----------------------------------|

**Equipment**

---

|                              |     |
|------------------------------|-----|
| Number of rows               | 8   |
| Quantity of section in width | 2   |
| Number of keys               | 1   |
| Quantity of rails            | 8   |
| Can be accessorized          | Yes |
| Extension possible           | Yes |
| Earthing terminal block      | Yes |
| Neutral terminal block       | Yes |
| Signal passing door          | No  |

**Standards**

---

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

**Safety**

---

|                     |               |
|---------------------|---------------|
| Protection index IP | IP44          |
| Protection class    | isol.class II |
| REACH conform       | No            |
| RoHS conform        | Yes           |
| Halogen free        | No            |