



FWB42S

FWB encl. univers,4-rows 96 modules cl.II IP44 w.plain door, 650x550x161mm,QC

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
Protection main switch	No

Configuration

Number of modules	96
-------------------	----

Compatibility

Suitable for Multimedia	No
-------------------------	----

Electric current

Rated current	125 A
---------------	-------

Dimensions

Insertion depth	161 mm
Depth of installed product	165 mm
Internal depth	156 mm
Height of installed product	650 mm
Installation height	650 mm
Width of installed product	550 mm
Width in division units	24
Thickness of sidewall material	1 mm

Cover, door

Number of keylock of the door	1
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Copper weight of the product	0.081 kg
Colour	white
RAL colour	RAL 9010 - Pure white
Material	sheet steel

Installation, mounting

Subject to technical modifications

Suitable for outdoor use	No
Connection	
Number of conduit inlets	8
Equipment	
Number of rows	4
Quantity of section in width	2
Number of keys	1
Quantity of rails	8
Can be accessorized	Yes
Number of openings for flange plates	4
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	No
Standards	
GWT Glow wire test	750 °C
European directive WEEE	concerned
Protection class according to IEC-61140	II
Safety	
Protection index IP	IP44
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No