



FWB42S

FWB encl. univers,4-rows 96 modules cl.II IP44 w.plain door, 650x550x161mm,QC

Technical properties

Functions

With a pipe-in lead	Yes
Protection main switch	No

Configuration

Module	with terminals
Number of modules	96

Compatibility

Suitable for Multimedia	No
-------------------------	----

Electric current

Rated current	125 A
---------------	-------

Dimensions

Insertion depth	161 mm
Depth of installed product	165 mm
Internal depth	156 mm
Height of installed product	650 mm
Installation height	650 mm
Width of installed product	550 mm
Width in division units	24
Thickness of sidewall material	1 mm

Cover, door

Type of door closing	hinged pattern handle
Number of keylock of the door	1
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Copper weight of the product	0.081 kg
Colour	white
RAL colour	RAL 9010 - Pure white
Material	sheet steel

Installation, mounting

Suitable for outdoor use No

Connection

Number of conduit inlets 8

Settings

Enclosure type Field distributor surface mounted

Equipment

Number of rows 4

Quantity of section in width 2

Number of keys 1

Quantity of rails 8

Can be accessorized Yes

Number of openings for flange plates 4

Extension possible Yes

Earthing terminal block Yes

Neutral terminal block Yes

Signal passing door No

Standards

GWT Glow wire test 750 °C

Protection class according to IEC-61140 II

Safety

IK protection code against mechanical impacts 09

Protection index IP IP44

Protection class isol.class II

REACH conform No

RoHS conform Yes

Halogen free No

Impact strength IK09