



FWB51

FWB encl.,univers,5rows 60 mod cl.II IP44,plain door,800x300x161mm,brass term.

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes
 Protection main switch No

Configuration

Number of modules 60

Compatibility

Suitable for Multimedia No

Electric current

Rated current 125 A

Dimensions

Insertion depth 161 mm
 Depth of installed product 165 mm
 Internal depth 156 mm
 Height of installed product 800 mm
 Installation height 800 mm
 Width of installed product 300 mm
 Width in division units 12
 Thickness of sidewall material 1 mm

Cover, door

Type of door closing hinged pattern handle
 Number of keylock of the door 1
 Cover type Closed (plain)
 Door locking without
 Door leave single
 Cover type Door
 Transparent cover or door No

Materials

Colour white
 Colour white
 RAL colour RAL 9010 - Pure white
 Material Steel

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Number of conduit inlets	4
--------------------------	---

Settings

Enclosure type	Field distributor surface mounted
----------------	-----------------------------------

Equipment

Number of rows	5
----------------	---

Quantity of section in width	1
------------------------------	---

Number of keys	1
----------------	---

Quantity of rails	5
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	2
--------------------------------------	---

Extension possible	Yes
--------------------	-----

Earthing terminal block	No
-------------------------	----

Neutral terminal block	Yes
------------------------	-----

Signal passing door	No
---------------------	----

Standards

GWT Glow wire test	750 °C
--------------------	--------

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP44
---------------------	------

Protection class	isol.class II
------------------	---------------